



SN10B, Nylon Splice For 12 - 10 AWG

By Burndy
Catalog # [SN10B](#)

Nylon Splice For 12 - 10 AWG



Features

- Tin plated copper brazed butt seam
- Smooth funnel entry for easy wire insertion
- Mylon insulation offers high dielectric strength and stability

Application

For Heavy Duty Application Requirements

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	10 - 12 AWG

Configuration

Connector Type	Brazed Seam Butt Splice
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.22 in
Dimension - L Length Overall mm	42 mm
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	1.64 in

General

Sub Brand	INSULINK
Insulation Type	Nylon
Color Code	Yellow
Trade Name	INSULINK™
Plated	Y
Insulation	Y
Type	SN
UPC 12 Digit	781810525081
UPC 14 Digit GTIN	00781810525081
Material	Copper
Plating Type	Tin
UPC	781810525081

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)