



T1012, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [T1012](#)



Uninsulated Ring Terminal For 12 - 10 AWG

Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	22
Conductor - Copper Solid Size Range	22
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Package Length	4.230 in
Package Width	3.000 in
Package Weight	0.265 lb.
Dimension - Z inch	0.61 in
Dimension - L Length Overall mm	31 mm
Dimension - Pad Width inch	0.69 in
Package Height	1.500 in
Dimension - Bolt Size fraction	1/2
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Length Overall inch	1.21 in

General

Sub Brand	TERMINALS, HYDENT
Physical Attribute - Tongue Type	Ring
Trade Name	HYDENT™
Plated	Y
Feature - Barrel Type	Long
Type	Ring Tongue
UPC 12 Digit	781810525630
UPC 14 Digit GTIN	00781810525630
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810525630

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)