

T1014, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [T1014](#)

Uninsulated Ring Terminal For 12 - 10 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	25 mm
Dimension - Pad Width inch	0.46 in
Package Height	0.000 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	1/4
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Z inch	0.39 in
Dimension - Bolt Size fraction	1/4
Cable Insulation Diameter Maximum	0.120 in
Dimension - Length Overall inch	0.97 in
Dimension - Diameter Max Size inch	0.12 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Long
Type	Ring Tongue
UPC 12 Digit	781810722121
UPC 14 Digit GTIN	00781810722121
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810722121

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999



A Hubbell brand