

T1014F, Fork Terminal, 12-10 AWG, 1/4" Stud

By Burndy
Catalog # [T1014F](#)



Uninsulated Fork Terminal For 12 - 10 AWG, 1/4" Stud, Fork Design
Provides Faster Installation

Features

- Type T-F uninsulated fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork style permits rapid installation of the terminal under screw head without completely removing screw
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 10 AWG (Str.) • 12 AWG (Sol.) • 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 10 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - Z inch	0.39 in
Dimension - Length Overall inch	1.00 in

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Yes
Physical Attribute - Tongue Type	Fork
Sub Brand	HYLUG
Product Type	Terminal
UPC	781810722145
Type	T-F
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810722145
UPC 14 Digit GTIN	00781810722145

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)