



T106F, Uninsulated Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # T106F



Uninsulated Fork Terminal For 12 - 10 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	14 AWG 10 AWG (Str.) 12 AWG (Sol.) 10 AWG
Conductor - Copper Solid Size	12 AWG 11 AWG 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG

Conductor - Copper Str Size Range	14 AWG - 10 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	19 mm
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#4 #5 #6
Dimension - Z inch	0.25 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.74 in

General

Trade Name	HYLUG™
Sub Brand	TERMINALS, HYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	T-F, Compression Terminal
UPC 12 Digit	781810722022
UPC 14 Digit GTIN	00781810722022
Material	Copper
Plating Type	Tin
UPC	781810722022

Logistics

Minimum Pack Quantity	50
-----------------------	----

Carton Quantity600

Pallet Quantity99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand