



## T108, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [T108](#)

Uninsulated Ring Terminal For 12 - 10 AWG



### Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

### Application

For Control Wiring And Other Standard Duty Applications

### Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Industry Standard(s)               | UL467                |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL486                |
| Standards - RoHS Compliance Status | CM                   |
| Certification - CSA Approved       | Yes                  |
| UL Listed                          | Yes                  |

### Conductor

|                                     |                                                                                            |
|-------------------------------------|--------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>• 12 AWG</li><li>• 10 AWG</li></ul>                  |
| Conductor - Copper Solid Size       | <ul style="list-style-type: none"><li>• 12 AWG</li><li>• 11 AWG</li><li>• 10 AWG</li></ul> |
| Conductor - Copper Solid Size Range | 12 AWG-10 AWG                                                                              |
| Conductor Size                      | 12 - 10 AWG                                                                                |
| Conductor - Copper Str Size Range   | 12 AWG-10 AWG                                                                              |
| Conductor Type                      | <ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>  |

### Configuration

|                                      |               |
|--------------------------------------|---------------|
| Physical Attribute - Number of Holes | 1             |
| Connector Type                       | Ring Terminal |

### Dimensions

|                                    |                                                                   |
|------------------------------------|-------------------------------------------------------------------|
| Package Length                     | 0.000 in                                                          |
| Package Width                      | 0.000 in                                                          |
| Package Weight                     | 0.000 lb.                                                         |
| Dimension - L Length Overall mm    | 21 mm                                                             |
| Dimension - Pad Width inch         | 0.37 in                                                           |
| Package Height                     | 0.000 in                                                          |
| Dimension - Hole Size fraction     | 8/47                                                              |
| Dimension - Hole Size inch         | 0.17 in                                                           |
| Dimension - Strip Length inch      | 11/32                                                             |
| Dimension - Stud Size inch         | <ul style="list-style-type: none"><li>• #6</li><li>• #8</li></ul> |
| Dimension - B Length fraction      | 17/50 in                                                          |
| Dimension - B Length inch          | 0.34 in                                                           |
| Dimension - Z inch                 | 0.29 in                                                           |
| Dimension - Bolt Size fraction     | #6 - #8                                                           |
| Dimension - Length Overall inch    | 0.83 in                                                           |
| Dimension - Diameter Max Size inch | 0.12 in                                                           |

### General

|                                  |                      |
|----------------------------------|----------------------|
| Trade Name                       | HYLUG™               |
| Sub Brand                        | HYLUG                |
| Physical Attribute - Tongue Type | Ring                 |
| Plated                           | Y                    |
| Feature - Barrel Type            | Long                 |
| Type                             | Ring Tongue          |
| UPC 12 Digit                     | 781810722046         |
| UPC 14 Digit GTIN                | 00781810722046       |
| Material                         | Copper               |
| Plating Type                     | Tin - Electro Plated |
| UPC                              | 781810722046         |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Carton Quantity       | 600   |
| Pallet Quantity       | 99999 |



A Hubbell brand