



T1410F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [T1410F](#)



Uninsulated Fork Terminal For 16 - 14 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#20 AWG to #14 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------



A Hubbell brand

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	19
Dimension - Pad Width inch	0.37 in
Package Height	0.000 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#8 - #10
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Z inch	0.28 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Length Overall inch	0.73 in
Dimension - Diameter Max Size inch	0.07 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	T-F
UPC 12 Digit	781810722428
UPC 14 Digit GTIN	00781810722428
Material	Copper
Plating Type	Tin
UPC	781810722428

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)