

T146, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [T146](#)

Uninsulated Ring Terminal For 16 - 14 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#20 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	17
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#4 - #6
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Z inch	0.28 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.66 in
Dimension - Diameter Max Size inch	0.08 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Long
Type	Ring Tongue
UPC 12 Digit	781810722367
UPC 14 Digit GTIN	00781810722367
Material	Copper
Plating Type	Tin
UPC	781810722367

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)