

T1814F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [T1814F](#)



Uninsulated Fork Terminal For 22 - 18 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#22 AWG to #18 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	23
Dimension - Pad Width inch	0.47 in
Package Height	0.000 in
Dimension - Hole Size fraction	2/7
Dimension - Hole Size inch	0.28 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.39 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	0.92 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	T-F
UPC 12 Digit	781810723142
UPC 14 Digit GTIN	00781810723142
Material	Copper
Plating Type	Tin
UPC	781810723142

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)