



# T188F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # [T188F](#)

Uninsulated Fork Terminal For 22 - 18 AWG



## Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

## Application

For Control Wiring And Other Standard Duty Applications

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Industry Standard(s)               | UL467                |
| Buy America(n) Qualified           | Contact Manufacturer |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL486                |
| Standards - RoHS Compliance Status | CM                   |
| Certification - CSA Approved       | Yes                  |
| UL Listed                          | Yes                  |

## Conductor

|                 |                                                                                       |
|-----------------|---------------------------------------------------------------------------------------|
| Conductor Size  | 22 - 18 AWG                                                                           |
| Conductor Type  | <ul style="list-style-type: none"><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul> |
| Conductor Range | #22 AWG to #18 AWG                                                                    |

## Configuration

|                |               |
|----------------|---------------|
| Connector Type | Fork Terminal |
|----------------|---------------|

## Dimensions

|                                    |           |
|------------------------------------|-----------|
| Package Length                     | 0.000 in  |
| Package Width                      | 0.000 in  |
| Package Weight                     | 0.000 lb. |
| Dimension - L Length Overall mm    | 19        |
| Dimension - Pad Width inch         | 0.31 in   |
| Package Height                     | 0.000 in  |
| Dimension - Hole Size fraction     | 1/6       |
| Dimension - Hole Size inch         | 0.18 in   |
| Dimension - Strip Length inch      | 9/32 in   |
| Dimension - Stud Size inch         | #6 - #8   |
| Dimension - B Length fraction      | 13/50 in  |
| Dimension - B Length inch          | 0.26 in   |
| Dimension - Z inch                 | 0.27 in   |
| Dimension - Bolt Size fraction     | #6 - #8   |
| Dimension - Length Overall inch    | 0.73 in   |
| Dimension - Diameter Max Size inch | 0.06 in   |

## General

|                                  |                |
|----------------------------------|----------------|
| Trade Name                       | HYLUG™         |
| Sub Brand                        | HYLUG          |
| Physical Attribute - Tongue Type | Fork           |
| Plated                           | Y              |
| Feature - Barrel Type            | Long           |
| Feature - Barrel Style           | Chamfered      |
| Type                             | T-F            |
| UPC 12 Digit                     | 781810723067   |
| UPC 14 Digit GTIN                | 00781810723067 |
| Material                         | Copper         |
| Plating Type                     | Tin            |
| UPC                              | 781810723067   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Carton Quantity       | 1200  |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand