



TMH268SS, Stainless Steel Hardware Kit

By Burndy
Catalog # [TMH268SS](#)

Hardware Kit, Installation Torque: 240 IN-LB, Working Range:
0.44 - 0.69 IN



Features

- TMH Tongue Mounted Hardware Kits ensure the proper type and amount of hardware necessary for each installation
- Packaged in separate sealed bags, they are convenient to use and eliminate mismatched quantities

Application

A general purpose Fastening Hardware Kit providing long lasting corrosion resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Hardware
----------------	----------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Bolt Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Thread Size	3/8 - 16
Dimension - Threads per inch	16

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Sub Brand	HARDWARE KITS
UPC	781810271414
Type	TMHSS
Material	Stainless Steel
UPC 12 Digit	781810271414
UPC 14 Digit GTIN	00781810271414

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5568
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)