



TMHG42, Stainless Steel Hardware Kit for I-Beam Connector (not included)

By Burndy
Catalog # [TMHG42](#)

Stainless steel hardware kit



Features

- TMH Tongue Mounted Hardware Kits ensure the proper type and amount of hardware necessary for each installation
- Packaged in separate sealed bags, they are convenient to use and eliminate mismatched quantities

Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A-B • IEEE 837
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL 486A-B • IEEE 837
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Hardware
----------------	----------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Thread Size	1/2 - 13

General

Sub Brand	INSULUG
UPC	781810035054
Type	Compression Ground Connector
Material	Stainless Steel
UPC 12 Digit	781810035054
UPC 14 Digit GTIN	00781810035054

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5568
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)