



TMHG92, Stainless Steel Hardware Kit for I-Beam Connector (not included)

By Burndy
Catalog # [TMHG92](#)

Stainless steel hardware kit



Features

- TMH Tongue Mounted Hardware Kits ensure the proper type and amount of hardware necessary for each installation
- Packaged in separate sealed bags, they are convenient to use and eliminate mismatched quantities

Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A-B • IEEE 837
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL 486A-B • IEEE 837
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Hardware
----------------	----------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Thread Size	1/2 - 13

General

Sub Brand	INSULUG
UPC	781810035061
Type	Compression Ground Connector
Material	Stainless Steel
UPC 12 Digit	781810035061
UPC 14 Digit GTIN	00781810035061

Logistics

Minimum Pack Quantity	12
Pallet Quantity	5568
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)