



TN1010BF, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN1010BF](#)

Nylon Block Fork Terminal For 12 - 10 AWG



Features

- Permits rapid and easy installation of the terminal under the screw head without complete removal of the screw

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.35 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#8 - #10
Dimension - Length Overall inch	1.02 in

General

Sub Brand	HYDENT
Insulation Type	Nylon
Physical Attribute - Tongue Type	Block Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	Fork Tongue
UPC 12 Digit	781810524091
UPC 14 Digit GTIN	00781810524091
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810524091

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)