



TN106F, Nylon Fork Terminal For 12 - 10 AWG

By Burndy

Catalog # [TN106F](#)

Nylon Fork Terminal For 12 - 10 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL486
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#10 AWG to #12 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------



A Hubbell brand

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Z inch	0.24 in
Dimension - Bolt Size fraction	#4 - #6
Cable Insulation Diameter Maximum	0.209 in
Dimension - Length Overall inch	0.96 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Yellow
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	TN-F
UPC 14 Digit GTIN	00781810732106
Material	Copper
Plating Type	Tin
UPC	781810732106

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)