



# TN146BF, Nylon Block Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # [TN146BF](#)

Nylon Block Fork Terminal For 16 - 14 AWG



## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## Application

Power Connector

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Certification - ETL                | No                   |
| Standards - RoHS Compliance Status | CM                   |
| Certification - CSA Approved       | No                   |
| UL Listed                          | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |

## Conductor

|                 |                                                                                           |
|-----------------|-------------------------------------------------------------------------------------------|
| Conductor Size  | 16 - 14 AWG                                                                               |
| Conductor Type  | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor Range | #14 AWG to #16 AWG                                                                        |

## Configuration

|                |                     |
|----------------|---------------------|
| Connector Type | Block Fork Terminal |
|----------------|---------------------|

## Dimensions

|                |           |
|----------------|-----------|
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |
| Package Weight | 0.000 lb. |

|                                 |                                                                                |
|---------------------------------|--------------------------------------------------------------------------------|
| Dimension - Z inch              | 0.30 in                                                                        |
| Dimension - L Length Overall mm | 24 mm                                                                          |
| Dimension - Pad Width inch      | 0.25 in                                                                        |
| Package Height                  | 0.000 in                                                                       |
| Dimension - Bolt Size fraction  | #4 - #6                                                                        |
| Dimension - Strip Length inch   | 3/16                                                                           |
| Dimension - Stud Size inch      | <ul style="list-style-type: none"><li>• #4</li><li>• #5</li><li>• #6</li></ul> |
| Dimension - Length Overall inch | 0.93 in                                                                        |

## General

|                                  |                      |
|----------------------------------|----------------------|
| Sub Brand                        | HYDENT               |
| Insulation Type                  | Nylon                |
| Physical Attribute - Tongue Type | Fork                 |
| Trade Name                       | HYDENT™              |
| Plated                           | Y                    |
| Insulation                       | Y                    |
| Type                             | Fork Tongue          |
| UPC 14 Digit GTIN                | 00781810524183       |
| Material                         | Copper               |
| Plating Type                     | Tin - Electro Plated |
| UPC                              | 781810524183         |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
| Carton Quantity       | 100 |
| Pallet Quantity       | 1   |

## Product Assets

[Catalog \[English\]](#)