

TN202F, Nylon Fork Terminal For 26 - 20 AWG

By Burndy
Catalog # [TN202F](#)

Nylon Fork Terminal For 26 - 20 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	20 AWG
Conductor Size	26 - 20 AWG
Conductor - Copper Str Size Range	20 AWG
Conductor Type	CU C Str-Size
Conductor Range	#20 AWG to #26 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------

Current

Voltage - Maximum	300 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	19 mm
Dimension - Pad Width inch	0.18 in
Package Height	0.000 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#1 #2
Dimension - Z inch	0.24 in
Dimension - Bolt Size fraction	#1 - #2
Cable Insulation Diameter	0.098 in
Maximum	
Dimension - Length Overall	0.76 in
inch	

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Amber
Physical Attribute - Tongue	Fork
Type	
Plated	Y
Feature - Barrel Style	Shrouded
Type	TN-F
UPC 14 Digit GTIN	00781810734919
Material	Copper
Plating Type	Tin
UPC	781810734919

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand