



## TN206F, Nylon Fork Terminal For 26 - 20 AWG

By Burndy  
Catalog # [TN206F](#)

Nylon Fork Terminal For 26 - 20 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

Power Connector

Specifications

|                               |                      |
|-------------------------------|----------------------|
| Buy American Compliant        | Contact Manufacturer |
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |


Conductor

|                             |                    |
|-----------------------------|--------------------|
| Conductor - Copper Str Size | 20 AWG             |
| Conductor Size              | 26 - 20 AWG        |
| Conductor - Copper Str Size | 20 AWG             |
| Range                       |                    |
| Conductor Type              | CU C Str-Size      |
| Conductor Range             | #20 AWG to #26 AWG |

Configuration

|                |               |
|----------------|---------------|
| Connector Type | Fork Terminal |
|----------------|---------------|

Current



|                   |       |
|-------------------|-------|
| Voltage - Maximum | 300 V |
|-------------------|-------|

Dimensions

|                                |                                                                                |
|--------------------------------|--------------------------------------------------------------------------------|
| Package Length                 | 0.000 in                                                                       |
| Package Width                  | 0.000 in                                                                       |
| Package Weight                 | 0.000 lb.                                                                      |
| Dimension - L Length Overall   | 20 mm                                                                          |
| mm                             |                                                                                |
| Dimension - Pad Width inch     | 0.28 in                                                                        |
| Package Height                 | 0.000 in                                                                       |
| Dimension - Strip Length inch  | 3/16                                                                           |
| Dimension - Stud Size inch     | <ul style="list-style-type: none"><li>• #4</li><li>• #5</li><li>• #6</li></ul> |
| Dimension - Z inch             | 0.28 in                                                                        |
| Dimension - Bolt Size fraction | #4 - #6                                                                        |
| Cable Insulation Diameter      | 0.098 in                                                                       |
| Maximum                        |                                                                                |
| Dimension - Length Overall     | 0.80 in                                                                        |
| inch                           |                                                                                |

General

|                             |                |
|-----------------------------|----------------|
| Insulation Type             | Nylon          |
| Trade Name                  | INSULUG™       |
| Insulation                  | Y              |
| Sub Brand                   | INSULUG        |
| Color Code                  | Amber          |
| Physical Attribute - Tongue | Fork           |
| Type                        |                |
| Plated                      | Y              |
| Feature - Barrel Style      | Shrouded       |
| Type                        | TN-F           |
| UPC 14 Digit GTIN           | 00781810734957 |
| Material                    | Copper         |
| Plating Type                | Tin            |
| UPC                         | 781810734957   |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Carton Quantity       | 1200  |
| Pallet Quantity       | 99999 |

Product Assets

[Catalog \[English\]](#)