



TP1010BF, Vinyl Block Fork Terminal, 12-10 AWG, #8-10 Stud

By Burndy
Catalog # [TP1010BF](#)

Vinyl Block Fork Terminal For 12 - 10 AWG, #8-10 Stud, Rapid, Easy Installation

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Dimension - Pad Width inch	0.35 in
Package Height	3.000 in
Dimension - Bolt Size fraction	#8 - #10
Package Weight	0.450 lb.

Package Length	4.250 in
Package Width	3.000 in
Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Cable Insulation Diameter Maximum	0.280 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	#8 - #10

General

Feature - Barrel Style	Shrouded
Plated	Yes
Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Block Fork
Sub Brand	HYDENT
Product Type	Terminal
UPC	781810524282
Type	Fork Tongue
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810524282
UPC 14 Digit GTIN	00781810524282

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)