



# TP108BF, Vinyl Block Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [TP108BF](#)



Vinyl Block Fork Terminal For 12 - 10 AWG

## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## Specifications

|                               |                      |
|-------------------------------|----------------------|
| Buy American Compliant        | Contact Manufacturer |
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |

## Conductor

|                 |                    |
|-----------------|--------------------|
| Conductor Size  | 12 - 10 AWG        |
| Conductor Type  | CU C Str-Size      |
| Conductor Range | #12 AWG to #10 AWG |

## Configuration

|                |                     |
|----------------|---------------------|
| Connector Type | Block Fork Terminal |
|----------------|---------------------|

## Dimensions

|                    |           |
|--------------------|-----------|
| Package Length     | 4.000 in  |
| Package Width      | 3.000 in  |
| Package Weight     | 0.220 lb. |
| Dimension - Z inch | 0.29 in   |

|                                |          |
|--------------------------------|----------|
| Dimension - L Length Overall   | 26 mm    |
| Dimension - Pad Width inch     | 0.33 in  |
| Package Height                 | 1.500 in |
| Dimension - Bolt Size fraction | #6 - #8  |
| Dimension - Strip Length inch  | 19/64 in |
| Dimension - Stud Size inch     | #6 - #8  |
| Cable Insulation Diameter      | 0.260 in |
| Maximum                        |          |
| Dimension - Length Overall     | 1.02 in  |
| inch                           |          |

## General

|                             |                |
|-----------------------------|----------------|
| Sub Brand                   | HYDENT         |
| Insulation Type             | Vinyl          |
| Physical Attribute - Tongue | Block Fork     |
| Type                        |                |
| Trade Name                  | VINYLUG™       |
| Plated                      | Y              |
| Feature - Barrel Style      | Shrouded       |
| Insulation                  | Y              |
| Type                        | Fork Tongue    |
| UPC 12 Digit                | 781810524329   |
| UPC 14 Digit GTIN           | 00781810524329 |
| Material                    | Copper         |
| Plating Type                | Tin            |
| UPC                         | 781810524329   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Carton Quantity       | 100   |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)