



TP108LF, Vinyl Locking Fork Terminal, 12-10 AWG, #8 Stud

By Burndy
Catalog # [TP108LF](#)



Vinyl Locking Fork Terminal For 12 - 10 AWG, #8 Stud, Fast Installation with Security

Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#8
Dimension - Bolt Size fraction	#8
Dimension - B Length fraction	17/50 in
Dimension - Z inch	0.26 in
Dimension - B Length inch	0.34 in
Dimension - Length Overall inch	1.07
Cable Insulation Diameter Maximum	0.260 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Yellow
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810713853
Type	TP-LF, Locking
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810713853
UPC 14 Digit GTIN	00781810713853

Logistics

Pallet Quantity	99999
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)