

TP108Z, Vinyl Flanged Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP108Z](#)



Vinyl Flanged Fork Terminal For 12 - 10 AWG

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Fast Installation And Security

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flanged Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.26 in
Dimension - Bolt Size fraction	#8
Cable Insulation Diameter Maximum	0.260 in
Dimension - Length Overall inch	1.01 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Color Code	Yellow
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	Flange Fork
UPC 12 Digit	781810710760
UPC 14 Digit GTIN	00781810710760
Material	Copper
Plating Type	Tin
UPC	781810710760

Logistics

Minimum Pack Quantity	10000
Carton Quantity	10000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)