



# TP1410RBG25, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [TP1410RBG25](#)



Vinyl Ring Terminal For 16 - 14 AWG

### Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

### Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - cULus              | No    |
| Certification - UL Recognized      | No    |
| Certification - ETL                | No    |
| Standards - Industry Standards Met | UL486 |
| Standards - RoHS Compliance Status | CM    |
| Certification - CSA Approved       | Yes   |
| UL Listed                          | Yes   |

### Conductor

|                                     |                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size       | <ul style="list-style-type: none"><li>16 AWG</li><li>15 AWG</li><li>14 AWG</li></ul> |
| Conductor - Copper Solid Size Range | 16 AWG-14 AWG                                                                        |
| Conductor Size                      | 16 - 14 AWG                                                                          |
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>16 AWG</li><li>14 AWG</li></ul>                |
| Conductor - Copper Str Size Range   | 16 AWG - 14 AWG                                                                      |
| Conductor Type                      | <ul style="list-style-type: none"><li>CU C Solid-Size</li></ul>                      |

- CU C Str-Size

### Configuration

|                                      |               |
|--------------------------------------|---------------|
| Physical Attribute - Number of Holes | 1             |
| Connector Type                       | Ring Terminal |

### Dimensions

|                                |           |
|--------------------------------|-----------|
| Package Length                 | 0.000 in  |
| Package Width                  | 0.000 in  |
| Package Weight                 | 0.000 lb. |
| Package Height                 | 0.000 in  |
| Dimension - Bolt Size fraction | #10       |
| Dimension - Stud Size inch     | #10       |

### General

|                   |                |
|-------------------|----------------|
| Insulation Type   | Vinyl          |
| Trade Name        | HYDENT™        |
| Plated            | Y              |
| Insulation        | Y              |
| Type              | Ring Tongue    |
| UPC 12 Digit      | 781810486450   |
| UPC 14 Digit GTIN | 00781810486450 |
| Material          | Copper         |
| Plating Type      | Tin            |
| UPC               | 781810486450   |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 5     |
| Carton Quantity       | 5     |
| Pallet Quantity       | 11625 |

### Product Assets

[Catalog \[English\]](#)