



TP142F, Vinyl Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP142F](#)



Vinyl Fork Terminal For 16 - 14 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	20 mm
Dimension - Pad Width inch	0.17 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#2
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Z inch	0.23 in
Dimension - Bolt Size fraction	#2
Cable Insulation Diameter Maximum	0.180 in
Dimension - Length Overall inch	0.75 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Color Code	Blue
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	TP-F, Compression Terminal
UPC 12 Digit	781810712122
UPC 14 Digit GTIN	00781810712122
Material	Copper
Plating Type	Tin
UPC	781810712122

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999



A Hubbell brand