

TP162Z, Vinyl Flanged Fork Terminal, 22-16 AWG, #2 Stud

By Burndy
Catalog # [TP162Z](#)



Vinyl Flanged Fork Terminal For 22 - 16 AWG, #2 Stud, Flange Fork Design Makes Re-Securing Easier

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	• #20 AWG to #22 AWG • 16 AWG to 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flanged Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.17 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	8/89
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	20 mm
Dimension - Hole Size inch	0.09 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#2
Dimension - Bolt Size fraction	#2
Dimension - Z inch	0.23 in
Dimension - Length Overall inch	0.78 in
Cable Insulation Diameter Maximum	0.145 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Red
Physical Attribute - Tongue Type	Flanged Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810714201
Type	Flange Fork
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810714201
UPC 14 Digit GTIN	00781810714201

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)