



# TP166BF, Vinyl Block Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # [TP166BF](#)



Vinyl Block Fork Terminal For 22 - 16 AWG

## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Certification - ETL                | No                   |
| Standards - RoHS Compliance Status | CM                   |
| Certification - CSA Approved       | No                   |
| UL Listed                          | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |

## Conductor

|                 |                                                                                           |
|-----------------|-------------------------------------------------------------------------------------------|
| Conductor Size  | 22 - 16 AWG                                                                               |
| Conductor Type  | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor Range | #22 AWG to #18 AWG                                                                        |

## Configuration

|                |                     |
|----------------|---------------------|
| Connector Type | Block Fork Terminal |
|----------------|---------------------|

## Dimensions

|                |           |
|----------------|-----------|
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |
| Package Weight | 0.000 lb. |

|                                   |          |
|-----------------------------------|----------|
| Dimension - Z inch                | 0.32 in  |
| Dimension - L Length Overall mm   | 24 mm    |
| Dimension - Pad Width inch        | 0.25 in  |
| Package Height                    | 0.000 in |
| Dimension - Bolt Size fraction    | #4 - #6  |
| Dimension - Strip Length inch     | 13/64 in |
| Dimension - Stud Size inch        | #4 - #6  |
| Cable Insulation Diameter Maximum | 0.145 in |
| Dimension - Length Overall inch   | 0.95 in  |

## General

|                                  |                |
|----------------------------------|----------------|
| Sub Brand                        | HYDENT         |
| Insulation Type                  | Vinyl          |
| Physical Attribute - Tongue Type | Block Fork     |
| Trade Name                       | VINYLUG™       |
| Plated                           | Y              |
| Feature - Barrel Style           | Shrouded       |
| Insulation Type                  | Y              |
| Type                             | Fork Tongue    |
| UPC 12 Digit                     | 781810524381   |
| UPC 14 Digit GTIN                | 00781810524381 |
| Material                         | Copper         |
| Plating Type                     | Tin            |
| UPC                              | 781810524381   |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 100  |
| Carton Quantity       | 100  |
| Pallet Quantity       | 3600 |

## Product Assets

[Catalog \[English\]](#)