

TP166LF, Vinyl Locking Fork Terminal, 22-16 AWG, #6 Stud

By Burndy
Catalog # [TP166LF](#)

Vinyl Locking Fork Terminal For 22 - 16 AWG, #6, Fork Design for Faster Installation



Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	• #20 AWG to #22 AWG • 16 AWG to 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.28 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Hole Size inch	0.14 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#6
Dimension - Bolt Size fraction	#6
Dimension - Z inch	0.23 in
Dimension - Length Overall inch	0.87 in
Cable Insulation Diameter Maximum	0.145 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Red
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810713501
Type	TP-LF, Locking
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810713501
UPC 14 Digit GTIN	00781810713501

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)