



# TP168Z, Vinyl Flanged Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # [TP168Z](#)



Vinyl Flanged Fork Terminal For 22 - 16 AWG

## Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

## Application

For Fast Installation And Security

## Specifications

|                                |                      |
|--------------------------------|----------------------|
| Buy American Compliant         | Contact Manufacturer |
| Certification - cULus          | No                   |
| EU RoHS Indicator              | Yes                  |
| Certification - UL Recognized  | No                   |
| Certification - ETL            | No                   |
| Standards - Industry Standards | UL486                |
| Met                            |                      |
| Standards - RoHS Compliance    | CM                   |
| Status                         |                      |
| Certification - CSA Approved   | Yes                  |
| UL Listed                      | Yes                  |

## Conductor

|                 |                                                                                                 |
|-----------------|-------------------------------------------------------------------------------------------------|
| Conductor Size  | 22 - 16 AWG                                                                                     |
| Conductor Type  | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>       |
| Conductor Range | <ul style="list-style-type: none"><li>• #20 AWG to #22 AWG</li><li>• 16 AWG to 18 AWG</li></ul> |

## Configuration

|                                      |                       |
|--------------------------------------|-----------------------|
| Physical Attribute - Number of Holes | 1                     |
| Connector Type                       | Flanged Fork Terminal |

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                |           |
|--------------------------------|-----------|
| Package Length                 | 0.000 in  |
| Package Width                  | 0.000 in  |
| Package Weight                 | 0.000 lb. |
| Dimension - L Length Overall   | 22 mm     |
| Dimension - Pad Width inch     | 0.31 in   |
| Package Height                 | 0.000 in  |
| Dimension - Hole Size fraction | 9/53      |
| Dimension - Hole Size inch     | 0.17 in   |
| Dimension - Strip Length inch  | 1/4 in    |
| Dimension - Stud Size inch     | #8        |
| Dimension - Z inch             | 0.26 in   |
| Dimension - Bolt Size fraction | #8        |
| Cable Insulation Diameter      | 0.145 in  |
| Maximum                        |           |
| Dimension - Length Overall     | 0.88 in   |
| inch                           |           |

## General

|                                  |                |
|----------------------------------|----------------|
| Insulation Type                  | Vinyl          |
| Trade Name                       | VINYLUG™       |
| Insulation                       | Y              |
| Sub Brand                        | VINYLUG        |
| Color Code                       | Red            |
| Physical Attribute - Tongue Type | Flanged Fork   |
| Plated                           | Y              |
| Feature - Barrel Style           | Shrouded       |
| Type                             | Flange Fork    |
| UPC 12 Digit                     | 781810714768   |
| UPC 14 Digit GTIN                | 00781810714768 |
| Material                         | Copper         |
| Plating Type                     | Tin            |
| UPC                              | 781810714768   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Carton Quantity       | 1200  |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)