



TP1810RBG25, Vinyl Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [TP1810RBG25](#)



Vinyl Ring Terminal For 22 - 18 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	20 18 AWG
Conductor - Copper Solid Size Range	20 -18 AWG
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	20 AWG 18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Bolt Size fraction	#10
Dimension - Stud Size inch	#10

General

Insulation Type	Vinyl
Trade Name	HYDENT™
Plated	Y
Insulation Type	Y
Type	Ring Tongue
UPC 12 Digit	781810486559
UPC 14 Digit GTIN	00781810486559
Material	Copper
Plating Type	Tin
UPC	781810486559

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)