



TTV10, Tap Connector For 12 - 10 AWG

By Burndy
Catalog # [TTV10](#)

Tap Connector For 12 - 10 AWG

Features

- Tap Connector that allows the user to tap into a wire mid-span without cutting or stripping the wire

Application

for an easy tap off of a run conductor

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Dimension - Width inch	0.38 in
Package Length	4.000 in
Dimension - Width mm	10 mm
Package Width	3.000 in
Package Weight	0.190 lb.
Dimension - L Length Overall mm	18 mm
Package Height	1.500 in
Dimension - Length Overall inch	0.72 in

General

Sub Brand	HYDENT
Color Code	Yellow
Trade Name	QIKTAP™
Type	Electrical Terminal
UPC 12 Digit	781810525111
UPC 14 Digit GTIN	00781810525111
UPC	781810525111

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)