



TTV14, Tap Connector For 16 - 14 AWG

By Burndy
Catalog # [TTV14](#)

Tap Connector For 16 - 14 AWG

Features

- Tap Connector that allows the user to tap into a wire mid-span without cutting or stripping the wire

Application

for an easy tap off of a run conductor

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	Insulation Piercing
----------------	---------------------

Dimensions

Dimension - Width inch	0.38 in
Package Length	0.000 in
Dimension - Width mm	10 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	18 mm
Package Height	0.000 in
Dimension - Length Overall inch	0.72 in

General

Sub Brand	HYDENT
Color Code	Blue
Trade Name	QIKTAP™
Type	Electrical Terminal
UPC 12 Digit	781810525128
UPC 14 Digit GTIN	00781810525128
UPC	781810525128

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)