



**U2HR155CG2, Substation Copper
Bus Support Clamp, 4/0 AWG Str-
1250 kcmil, Cu Pipe Size: 1/4"-1"
IPS, 5" Bolt Circle Dia**

By Burndy
Catalog # [U2HR155CG2](#)



Cast Cu Alloy Bus Support Clamp, CU Str. Size: 4/0 AWG -
1250 Kcmil, CU Pipe Size: 1/4"-1" IPS, 5 IN Bolt Circle Dia.

Application

Substation

General

Connector Type	Bus Support
Installation Torque	660 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810502792
UPC 12 Digit	7818105027922

Dimensions

Bolt Circle Diameter	5 in
Dimension - B Length inch	3.91 in
Dimension - G inch	2.12 in
Dimension - Height inch	3.72 in
Dimension - Width inch	8.75 in
Dimension - Width mm	222 mm

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil;1250 kcmil
Conductor - Copper Str Size Range	4/0 AWG-1250 kcmil
Conductor - Copper Tube Std Size	1/4 IPS;3/8 IPS;1/2 IPS;3/4 IPS;1 IPS
Conductor - Copper Tube Std Size Range	1/4 IPS-1 IPS

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[3D Models - U2HR155CG2_MODEL-STEP](#)
[3D Models - U2HR155CG2_MODEL-PDF](#)
[3D Models - U2HR155CG2_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSKC033306-01](#)



A proud member of the Hubbell Family.