



Stainless Steel Circular Non-Butting Twin U Die, 600 kcmil, Green, Index 22

By Burndy
Catalog # [U36RT](#)

12T U Die, 600 kcmil, Green, Index 22



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin U Style
- Color Code: Green
- Die Index 22

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	600 Kcmil
-----------------	-----------

Dimensions

Dimension - Width mm	19
Dimension - Width inch	0.75
Weight	0.20 lb.

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	• Use with Y35, Y750, PAT750 • Y46 and PAT46 with PUADP1 Adapter
Color Code	Green
Die Index	22
Die Type	U Die
UPC	781810627426
Type	Die
Construction Material - Main	Stainless Steel
UPC 12 Digit	781810627426
UPC 14 Digit GTIN	00781810627426

Logistics

Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)