



Stainless Steel Circular Non-Butting Twin U Die, 750 kcmil, 600 Flex, Black, Index 24

By Burndy
Catalog # [U39RT](#)

12T U Die, 750 kcmil, Black, Index 24



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin U Style
- Color Code: Black
- Die Index 24

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	750 Kcmil/600 Flex
-----------------	--------------------

Dimensions

Dimension - Width mm	35.00
Dimension - Width inch	1.38
Weight	0.26 lb.

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	• Use with Y35, Y750, PAT750 • Y46 and PAT46 with PUADP1 Adapter
Color Code	Black
Die Index	24
Die Type	U Die
UPC	781810627433
Type	Die
Construction Material - Main	Stainless Steel
UPC 12 Digit	781810627433
UPC 14 Digit GTIN	00781810627433

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)