



UC25R2R, TAPIT Aluminum Clamp

By Burndy
Catalog # [UC25R2R](#)



Cast Aluminum Alloy TAPIT™, 8 (SOL.) AWG-1/0 (Str.) AL & CU (Groove A), 6 AWG-1/0 AWG ACSR(Groove A), 8 (SOL.) AWG-2 (Str.) AWG CU (Groove B), 8 AWG-1 AWG ACSR (Groove B)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - AL Str Size A Range	8 AWG-1/0 AWG
Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0
Conductor - ACSR Str Run Range	6 AWG-1/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	42 in

Dimension - Height inch	1.66 in
Dimension - Height fraction	1-5/8 in
Dimension - B Length fraction	1-1/8 in
Package Weight	0.000 lb.
Dimension - Width mm	37 mm
Dimension - Width inch	1.45 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.125 in
Dimension - Width fraction	1-3/8 in

General

Plated	N
Trade Name	TAPIT™
UPC	781810092804
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810092804
UPC 14 Digit GTIN	00781810092804

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4750
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)