



UC2W28L, Cast Copper Alloy Universal Parallel Clamp

By Burndy

Catalog # [UC2W28L](#)

Cast Copper Alloy Universal Parallel Clamp, 2 Sol. - 4/0 Str, 1-1/8 Length, 1-3/4 in Width, Tin-plated



Features

- Interlocking finger design accommodates large range of conductor sizes
- Tin-plated, cast of high copper alloy and clamped with plated steel bolt

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201, 5005, Steel And Copperweld

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	• 9/32 (7) in • 5/16 (7) in • 3/8 (7) in • 7/16 (7) in • 1/2 (19) in • 9/16 (19) in
Conductor - AAAC 5005 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - Galvanized Steel Str Size Range	9/32 (7) in-9/16 (19) in
Conductor - AAAC 6201 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	• 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - AL Str Size Range	2 AWG-4/0 AWG

Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Str Size A	2 - 4/0
Conductor - Copper Str Size B	2 - 4/0
Conductor - Copper Str Size A Range	2 - 4/0
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - CopperWeld Solid Size Range	8 AWG-6 AWG
Conductor - CopperWeld C Solid Size	• 8 AWG • 7 AWG • 6 AWG
Conductor - AAAC 5005 Size	• 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor - Copper Str Size B Range	2 - 4/0

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.50 in
Dimension - Height fraction	1-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	1-3/4 in
Dimension - B Length fraction	1-1/8 in
Dimension - Width inch	1.75 in
Dimension - B Length inch	1.125 in

Force Related

Installation Torque Recommended	110 LBS/in in-lb
---------------------------------	------------------

General

Product Family	Utility Overhead & Underground Distribution>Mechanical Bolted Tap Connectors>Parallel Clamps	UPC 14 Digit GTIN	00781810094907
Plated	No	Logistics	
Sub Brand	TAPIT	Minimum Pack Quantity	1
Product Type	Mechanical	Pallet Quantity	4200
UPC	781810094907	Carton Quantity	50
Type	UC-L, Universal	Product Assets	
Material	Copper	Catalog [English]	
Plating Type	Tin		

