



# UC6W25CONKIT, Parallel Clamp Kit for Copper, includes UC Connector and Cover

By Burndy  
Catalog # [UC6W25CONKIT](#)



Parallel Clamp Kit for copper; included UC Connector and Cover

## Features

- Type UC-KIT includes Type UC Connector and Cover packaged together
- Type UC Connectors accommodate a large range of copper conductors in either groove

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                               |                                                                                                                                         |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size | 6 AWG                                                                                                                                   |
| Conductor - Copper Solid Size | 6 AWG                                                                                                                                   |
| Range                         |                                                                                                                                         |
| Conductor - Copper Str Size   | 6 AWG-1/0                                                                                                                               |
| Range                         |                                                                                                                                         |
| Conductor - Copper Str Size   | <ul style="list-style-type: none"><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li><li>• 1 AWG</li></ul> |

• 1/0

## Dimensions

|                               |           |
|-------------------------------|-----------|
| Package Height                | 0.000 in  |
| Dimension - Height mm         | 0 mm      |
| Dimension - Height fraction   | 1-5/8 in  |
| Dimension - B Length fraction | 1-3/4 in  |
| Package Weight                | 0.000 lb. |
| Package Length                | 0.000 in  |
| Package Width                 | 0.000 in  |
| Dimension - B Length inch     | 1.75 in   |
| Dimension - Width fraction    | 1-3/8 in  |

## General

|                   |                |
|-------------------|----------------|
| Plated            | N              |
| UPC               | 781810413128   |
| Plating Type      | Unplated       |
| UPC 12 Digit      | 781810413128   |
| UPC 14 Digit GTIN | 00781810413128 |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 20 |
| Pallet Quantity       | 1  |
| Carton Quantity       | 1  |

## Product Assets

[Catalog \[English\]](#)