



UC8W26L, Cast Copper Alloy Universal Parallel Clamp, Tin Plated

By Burndy

Catalog # [UC8W26L](#)

Cast Copper Alloy Universal Parallel Clamp, 8 Sol. - 2/0 Str, 1 in Length, 1-7/16 in Width, Tin-plated



Features

- Interlocking finger design accommodates large range of conductor sizes
- Tin-plated, cast of high copper alloy and clamped with plated steel bolt

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201, 5005, Steel And Copperweld

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	• 5/32 (7) in • 3/16 (7) in • 7/32 (7) in • 1/4 (7) in • 9/32 (7) in • 5/16 (7) in • 3/8 (7) in • 7/16 (7) in
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - Galvanized Steel Str Size Range	5/32 (7) in-7/16 (7) in
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil

Conductor - AL Str Size	• 246.9 (7) kcmil • 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Str Size A	8 - 2/0
Conductor - Copper Str Size B	8 - 2/0
Conductor - Copper Str Size A Range	8 - 2/0
Conductor - Copper Solid Size	8 -2/0
Conductor - Copper Solid Size Range	8 -2/0
Conductor - CopperWeld Solid Size Range	8 AWG-7 AWG
Conductor - CopperWeld C Solid Size	• 8 AWG • 7 AWG
Conductor - AAAC 5005 Size	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil • 155.4 (7) kcmil • 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - Copper Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size B Range	8 - 2/0

Dimensions

Package Height	0.000 in
Dimension - Height mm	38.1 mm
Dimension - Height inch	1.45 in

Dimension - Height fraction	1-1/2 in	Plated	Yes
Package Weight	0.000 lb.	Sub Brand	TAPIT
Package Length	0.000 in	Product Type	Mechanical
Package Width	0.000 in	UPC	781810095959
Dimension - Width fraction	1-7/16 in	Type	UC-L, Universal
Dimension - Width inch	1.48 in	Material	Copper
Dimension - B Length inch	1 in	Plating Type	Tin
		UPC 14 Digit GTIN	00781810095959
Force Related		Logistics	
Installation Torque Recommended	75 LBS/in	Minimum Pack Quantity	1
in-lb		Pallet Quantity	7200
General		Carton Quantity	150
Product Family	Utility Overhead & Underground Distribution>Mechanical Bolted Tap Connectors>Parallel Clamps	Product Assets	
		Catalog [English]	



A Hubbell brand