



UCG25RA2NS, Parallel Groove Clamp,
Groove A and B: Al/Cu 8 Str-1/0 Str, 6-1/0
ACSR, inhibitor included

By Burndy
Catalog # [UCG25RA2NS](#)

Multi-purpose parallel groove clamp

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Size A • CU C Solid-Size A • CU C Str-Size A • AAAC C 5005-Size A • AAAC C 6201-Size A • AL C Str-Size B • CU C Solid-Size B • CU C Str-Size B • AAAC C 5005-Size B • AAAC C 6201-Size B
----------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	TAPIT™
UPC	781810369616
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810369616
UPC 14 Digit GTIN	00781810369616

Logistics

Minimum Pack Quantity	1
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)