



UCG28R25RS, Cast Aluminum Alloy, 4-4/0
AWG ACSR (run), *-1/0 AWG Al (tap) 8-1/0
AWG ACSR (tap)

By Burndy
Catalog # [UCG28R25RS](#)

Cast Aluminum Alloy TAPIT™, 4 AWG-4/0 AWG ACSR (Run), 8
AWG-1/0 AWG AL Cable (Tap), 8 AWG-1/0 AWG ACSR (Tap)

Features

- TAPIT Parallel Clamp
- High strength, high conductivity, non-copper bearing aluminum alloy
- Properly proportioned to minimize stress corrosion and deterioration by galvanic action
- Keying tabs on connector body halves prevent mismatching
- Square shank, high strength galvanized steel bolt allows one wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Tap	8 AWG-1/0 AWG
Conductor - ACSR Str Run	4 (6-1) AWG-4/0 AWG
Range	
Conductor - ACSR Str Tap	8 AWG-1/0 AWG
Range	

Dimensions

Package Height	0.000 in
Dimension - Height mm	66 mm
Dimension - Height inch	2.60 in
Package Weight	0.000 lb.
Dimension - Width mm	49 mm
Dimension - Width inch	1.91 in
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	TAPIT™
UPC	781810012819
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810012819
UPC 14 Digit GTIN	00781810012819

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)