



UCK3UL, Interlocking-finger Parallel Clamp, #6-2 AWG Sol/Str for Both Grooves; Tin-Plated Copper

By Burndy
Catalog # [UCK3UL](#)

Interlocking-finger Parallel Clamp

Features

- Tin-plated cast copper alloy featuring interlocking-finger design
- Accommodates large range of conductor sizes
- Clamped with silicon bronze bolts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 8 AWG
	• 7 AWG
	• 6 AWG
	• 5 AWG
	• 4 AWG
	• 3 AWG
	• 2 AWG
	• 1 AWG
	• 1/0
	• 2/0 AWG
Conductor - Copper Str Size B	• 8 AWG
	• 7 AWG
	• 6 AWG
	• 5 AWG
	• 4 AWG
	• 3 AWG
	• 2 AWG
	• 1 AWG
	• 1/0
	• 2/0 AWG
Conductor - Copper Str Size A Range	6 Str. - 2 Str
Conductor - Copper Solid Size A Range	6 Sol. - 2 Sol



Conductor - Copper Solid Size B Range	6 Str. - 2 Str
Conductor - Copper Str Size B Range	6 Str. - 2 Str

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.5 mm
Dimension - Height inch	1.4375 in
Dimension - Height fraction	1-7/16 in
Package Weight	0.000 lb.
Dimension - Width mm	37 mm
Dimension - Width inch	1.4375 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Width fraction	1-7/16 in
Dimension - Length Overall inch	1 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810120866
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810120866
UPC 14 Digit GTIN	00781810120866

Logistics

Minimum Pack Quantity	20
Pallet Quantity	14400
Carton Quantity	150

Product Assets

[Catalog \[English\]](#)