



UCT26, FASTAP™ Series with LINEMAN ASSIST™ Series, Aluminum Parallel Groove Clamp. Run: Cu/Al 8 Sol-2/0, ACSR 6-2/0; Tap: Cu/Al 6 Sol-2/0, ACSR: 6-2/0

By Burndy
Catalog # [UCT26](#)

2/0 CU FASTAP PGC

Features

- Spring loaded feature that applies constant pressure on the conductor and acts as a third hand to hold the conductors in place to simplify installation
- Duckbill feature acts as a handle to easily hold the connector wearing dielectric gloveswhile
- The handle is especially handy in inclement weather
- The duckbill also acts as a lever to easily open the tap side of the conductor to slide the tap conductor in from the side
- The duckbill lastly acts as a guide to snap the conductor onto the Run conductor while the Lineman Assist™ feature holds onto the Tap conductor
- Conductor Side Entry simplifies installation of both the run and tap conductors
- Cover option eliminates brush contact with connection
- Expanded conductor range reduces the number of connectors required to satisfy most applications

Specifications

Certification - CSA Approved No

Conductor

Conductor Diameter (Main) - 0.45 in
Maximum
Conductor Diameter (Tap) - 0.13 in
Minimum
Conductor - Copper Str Size A 8 Sol - 2/0 Str
Range
Conductor - Copper Str Size B 8 Sol - 2/0 Str
Range



Conductor Diameter (Main) - 0.13 in
Minimum
Conductor Diameter (Tap) - 0.45 in
Maximum

Dimensions

Length 1.57 in
Width 2.67 in
Height 2.68 in
Dimensions 1.57 in x 2.67 in x 2.68 in

Force Related

Torque Rating 20 ft-lbs

General

Series FASTAP™ LINEMAN ASSIST™
Series
Plating No
Trade Name FASTAP™
UPC 14 Digit GTIN 00621945482647
Material Copper
Plating Type Unplated
UPC 621945482647

Logistics

Minimum Pack Quantity 1
Carton Quantity 1
Pallet Quantity 1

Product Assets

[Catalog \[English\]](#)