



UCT32RSSS, Aluminum Parallel Groove Clamp featuring LINEMAN ASSIST

By Burndy
Catalog # [UCT32RSSS](#)

BURNDY® FASTAP™ with LINEMAN ASSIST™ Aluminum Parallel Groove Clamp



Features

- Aluminum Parallel Groove Clamp with Lineman Assist

Application

The system helps secure both the Tap and Run conductors while installing on primary, secondary and service lines. Connector is not recommended for Copper to Copper applications

Specifications

Standards - RoHS Compliance	UI
Status	
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A Range	1 Sol. - 400
Conductor - Copper Solid Size	8-400
Conductor - AAAC 5005 Size Range	6 STR - 336.4
Conductor - AAAC 6201 Size Range	6 STR - 336.4
Conductor - Copper Solid Size Range	8-400
Conductor - AAAC 6201 Size	6 STR - 336.4
Conductor - AL Str Size A	1 SOL - 400
Conductor - AL Str Size B	8 SOL - 4/0 STR
Conductor - AL Str Size A Range	1 Sol. - 400
Conductor - AAAC 5005 Size	6 STR - 336.4
Conductor - AL Str Size B Range	8 Sol. - 4/0 Str.
Conductor Type	- AAAC C 5005-Size - AAAC C 6201-Size - ACSR C Str-Size - AL C Str-Size A - AL C Str-Size B - CU C Solid-Size

- CU C Str-Size A
- CU C Str-Size B
- CU Weld C Solid-Size

Conductor - ACSR Str Size	6 STR - 336.4
Conductor - ACSR Str Size A Range	2 Str. - 336.4
Conductor - Copper Str Size B Range	8 Sol. - 4/0 Str.
Conductor - ACSR Str Size B Range	6 Str. - 4/0

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	2.62 in
Package Weight	0.000 lb.
Dimension - Width inch	2.82 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	1.62 in

General

Plated	N
Trade Name	FASTAP™
Sub Brand	FASTAP
UPC	781810643884
Type	UCT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810643884
UPC 14 Digit GTIN	00781810643884

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1400
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)