



Stainless Steel U-Die Kit for Copper Connectors #6 AWG-750 kcmil (15 Sets). Color coded for crimping YA and YS types of connectors

By Burndy
Catalog # [UDIEKITCU](#)

12T U Die Kit (15) for Copper

Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin U Style (15 sets)

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	Copper: #6 AWG - 750 Kcmil
-----------------	----------------------------

Dimensions

Length	11.25 in
Weight	8.00 lb.
Height	3 in
Width	7.5 in
Dimensions	11.25 in x 7.5 in x 3 in

Force Related



Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	• Use with Y35, Y750, PAT750 • Y46 and PAT46 with PUADP1 Adapter
Tool Type	Die Kit, Copper
Die Type	U Die
UPC	781810478455
Type	Die
Construction Material - Main	Stainless Steel
UPC 12 Digit	781810478455
UPC 14 Digit GTIN	00781810478455

Logistics

Minimum Pack Quantity	1
Package Contents	(1 each) CASEUDIES15, U5CRT, U4CRT, U2CRT, U1CRT1, U25RT, U26RT, U27RT, U28RT, U29RT, U30RT, U31RT, U32RT, U34RT, U36RT, U39RT
Pallet Quantity	225
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)