

UGSKIT250, Watertight Underground Splice Kit, Dual Rated

By Burndy
Catalog # [UGSKIT250](#)

1 AWG-250 kcmil Dual Rated Mechanical Splice with 2 Heavy Wall Heat Shrink Sleeves, Al/Cu Rated



Features

- Type UGSKIT are underground splice kits (watertight) for aluminum or copper
- Kit consists of a standard splice/reducer and includes heavy wall heat-shrink sleeve
- Dual rated for use with aluminum and copper
- Connector is installed with common installation tools
- Both heavy wall heat shrink sleeves are lined with adhesive material providing a watertight splice

Application

For All Aluminum or Copper/Aluminum Combinations, UF Direct Burial

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL486D
Certification - ETL	No
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	1 AWG-250 kcmil
Conductor - Copper Str Size	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Conductor Size	1 AWG-250 KCMIL
Conductor - Copper Str Size Range	1 AWG-250 kcmil

Configuration

Connector Type	Splice/Heat Shrink Kit
----------------	------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in
Hex Size	5/16

General

Product Family	MECHANICAL
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	SPLICE KIT
Product Type	Splice Reducer
UPC	781810175286
Type	UGSKIT, Watertight/ Underground
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810175286

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)