




Stainless Steel UM Die Nest, #4 AWG DLO/Flex Cable

By Burndy
Catalog # [UM4CN](#)

12T UM Die Nest, #4 AWG DLO/Flex



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Nest UM Die
- #4 AWG DLO/Flex Cable

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	

Dimensions

Weight 0.21 lb.

Force Related

Crimp Force Capacity 12 ton

General

Application - For Use On	Use with OEM840NCP
	Pneumatic Press
Tool Type	OEM Pneumatic
Die Type	UM Die
UPC	781810656969
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810656969
UPC 14 Digit GTIN	00781810656969

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)

A Hubbell brand