



Stainless Steel Nest U Die, AN-6, Index 55, For YBM6CL Flag Terminals, Use with Y29PA1 indenter

By Burndy
Catalog # [UV6B1](#)

12T U Die Nest, #6 AWG Flag Crimp

Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Nest U Style
- Die Index 55
- Use with YBM6CL and Indenter Y29PBL

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length	1.57 in
Weight	0.50 lb.
Height	1.38 in
Width	1.06 in
Dimensions	1.57 in x 1.06 in x 1.38 in



Force Related

Crimp Force Capacity 12 ton

General

Application - For Use On	Use with Y29PA1 Indenter
Die Type	U Die
UPC	781810105597
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810105597
UPC 14 Digit GTIN	00781810105597

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)