



UW25R, CLIPIT Deadend Clamp, Aluminum Casting

By Burndy
Catalog # [UW25R](#)

CLIPIT deadend clamp. High strength aluminum casting with galvanized steel U-bolt. Holding strength of two deadends exceeds RBS of intended conductor.

Features

- CLIPIT Dead End Clamp Type UW-R
- High strength aluminum casting with galvanized steel U-bolt, extra long aluminum spacer, and caps that confine strands
- Holding strength of installations using two CLIPIT deadends exceeds rated breaking strength of conductor
- Use of PENETROX joint compound is recommended

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Tap Range	30.58 (7)-123.3 (7)
Conductor - AAAC 5005 Tap	• 30.58 (7) • 48.69 (7) • 77.47 (7) • 123.3 (7)
Conductor - AAAC 6201 Run Range	30.58 (7)-123.3 (7)
Conductor - AAAC 6201 Run	• 30.58 (7) • 48.69 (7) • 77.47 (7) • 123.3 (7)
Conductor - AAAC 5005 Size B	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil
Conductor - AAAC 5005 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7)-123.3 (7)



Conductor - AAAC 6201 Tap	• 30.58 (7) • 48.69 (7) • 77.47 (7) • 123.3 (7)
Conductor - AAAC 6201 Size A	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil
Conductor - AAAC 6201 Size B	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil
Conductor - AAAC 6201 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AL Str Size A	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Size B	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Size A Range	6 AWG-1/0 AWG
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - AL Str Size B Range	6 AWG-1/0 AWG
Conductor - AL Str Tap	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - ACSR Str Run Range	6 (6/1) Turkey-1/0 (6/1) Raven

Conductor - ACSR Str Run	• 6 (6/1) Turkey • 5 (6/1) Thrush • 4 (6/1) Swan • 4 (7/1) Swanate • 3 (6/1) Swallow • 2 (6/1) Sparrow • 2 (7/1) Sparate • 1 (6/1) Robin • 1/0 (6/1) Raven
Conductor - ACSR Str Tap Range	6 (6/1) Turkey-1/0 (6/1) Raven
Conductor - ACSR Str Tap	• 6 (6/1) Turkey • 5 (6/1) Thrush • 4 (6/1) Swan • 4 (7/1) Swanate • 3 (6/1) Swallow • 2 (6/1) Sparrow • 2 (7/1) Sparate • 1 (6/1) Robin • 1/0 (6/1) Raven
Conductor - AAAC 5005 Run Range	30.58 (7)-123.3 (7)
Conductor - AAAC 5005 Run	• 30.58 (7) • 48.69 (7) • 77.47 (7) • 123.3 (7)
Conductor - AAAC 5005 Size A	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil • 123.3 (7) kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	71.9 mm
Dimension - Height inch	2.83 in
Dimension - Height fraction	2-7/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Width fraction	2 in
Dimension - B Length fraction	1-46/63 in
Dimension - Width mm	50 mm
Dimension - Width inch	1.98 in
Dimension - B Length inch	1.73 in
Dimension - Length Overall inch	1.875 in

General

Trade Name	CLIPIT™
Material - Hardware	Galvanized Steel
Oxide Inhibitor Type	Penetrox A
Prefilled Oxide Inhibitor	Y
Plated	N
UPC	781810108000
Material	Aluminum Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810108000

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4500
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)

