



UW2R, Parallel Groove Clamp, Aluminum Casting

By Burndy
Catalog # [UW2R](#)

Parallel Groove Clamp with V-Bolts



Features

- CLIPIT Dead End Clamp Type UW-R
- High strength aluminum casting with galvanized steel U-bolt, extra long aluminum spacer, and caps that confine strands
- Holding strength of installations using two CLIPIT deadends exceeds rated breaking strength of conductor
- Use of PENETROX joint compound is recommended

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Run	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Run	• 30.58 (7) kcmil • 48.69 (7) kcmil

Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Height mm	65.5 mm
Dimension - Height inch	2.58 in
Dimension - Height fraction	2-5/8 in
Dimension - B Length fraction	1-1/2 in
Dimension - Width mm	46 mm
Dimension - Width inch	1.82 in
Dimension - L Length Overall mm	38 mm
Dimension - B Length inch	1.5 in
Dimension - Width fraction	1-7/8 in
Dimension - Length Overall inch	1.50 in

General

Plated	N
Trade Name	CLIPIT™
Material - Hardware	Galvanized Steel

Oxide Inhibitor Type	Penetrox A	Logistics	
UPC	781810107003	Minimum Pack Quantity	1
Prefilled Oxide Inhibitor	Y	Product Assets	
Material	Aluminum Alloy	Catalog [English]	
Plating Type	Unplated		
UPC 14 Digit GTIN	00781810107003		

