



Stainless Steel W Die, Index 162

By Burndy
Catalog # [W162](#)

6T W Die, Index 162



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index 162

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	Aluminum: #4 AWG
-----------------	------------------

Dimensions

Weight	0.14 lb.
--------	----------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Die Index	162
Die Type	W Die
UPC	781810440261
Type	W-Die for Hydraulic Crimping Tools (set)
Construction Material - Main	Stainless Steel
UPC 12 Digit	781810440261
UPC 14 Digit GTIN	00781810440261

Logistics

Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)